



Ergonomic Full Cycle Ratchet Crimper, For use on #22-#10 Nylon and Vinyl Insulated Terminals and Splices

By Burndy
Catalog # [MRE1022NV](#)



Full Cycle Ratchet Crimper, #22-#10 Nylon and Vinyl Insulated.

General

Application - For Use On	Nylon and Vinyl Insulated Terminals and Splices
Catalog Number	MRE1022NV
Die Type	Permanent Die Grooves
EU RoHS Indicator	Yes
Tool Type	Full Cycle Ratchet Crimper
Trade Name	HYTOOL™
UPC	781810512999
UPC 12 Digit	7818105129999

Dimensions

Dimensions	10.68 in x 3.00 in x 0.63 in
Height	0.63 in
Length	10.68 in
Weight	1.3 lb
Width	3 in

Conductor Related

Crimping Ranges	Copper: #22 AWG - #10 AWG
-----------------	---------------------------

Certifications And Compliance

Standards - RoHS Compliance	EX
Status	

Logistics

Package Contents	Tool only
------------------	-----------

Product Assets

- [Catalogs - Full Line BURNDY Catalog](#)
- [Catalogs - Section N - Tooling](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - BUR_30009440_SOMI_MRE10-22B and MRE10-22NV](#)
- [Product Cross Section Image\(s\) - BUR_MRE1022_lineart](#)
- [Sales Drawings - 30013557](#)



A proud member of the Hubbell Family.