

BIBS25014, Single Sided Fourteen Conductor Clear Insulated Multi-Tap Connector

By Burndy
Catalog # [BIBS25014](#)



MULTI-PORT Single-Sided Entry.

Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory

General

Catalog Number	BIBS25014
Connector Type	Multi Tap
Hex Key	5/16
Insulation	Y
Insulation Type	Plastisol
Material	Aluminum
Number Of Ports	14
Physical Attribute - Number of Screws	14
Physical Attribute - Screw Type	Allen
Plated	N
Plating Type	Unplated
Temperature Rating	194
Trade Name	UNITAP™
UPC	781810232989
UPC 12 Digit	7818102329899

Dimensions

Dimension - Height inch	2.13 in
Dimension - L Length Overall mm	338 mm
Dimension - Length Overall inch	13.29 in
Dimension - Width inch	2.07 in
Dimension - Width mm	53 mm

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - AL Str Size Range	10 - 250 Str
Conductor - Copper Str Size Range	10 - 250 Str
Conductor Size	10 AWG-250 KCMIL
Conductor Type	AL C Str-Size CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_BIBS_Lineart](#)
[Sales Drawings - sc210991-12](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY_CA-BIBS25014-SPEC-EN | REV 6/2024