



Substation - Connector

By Burndy
Catalog # [NBC24ACG3](#)

Substation Connectors.



Application

Substation

General

Catalog Number	NBC24ACG3
Connector Type	T-Connector
Installation Torque	660 LBS/in
Recommended in-lb	
Material	Aluminum Alloy
Material - Hardware	Aluminum
One Wrench Installation	Y
Physical Attribute - Number of Holes	4
Physical Attribute - Number of Run Conductors	1
Physical Attribute - Number of Tap Conductors	1
Physical Attribute - Pad Alignment	Centered
Physical Attribute - Pad Configuration	4 x 4 - 4 holes
Physical Attribute - Pad Orientation	Straight
Plated	N
Plating Type	Unplated
UPC	781810441107
UPC 12 Digit	7818104411077

Dimensions

Dimension - B Length inch	7.00 in
Dimension - D inch	4.00 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - G inch	7.69 in
Dimension - Height inch	6.44 in
Dimension - Hole Size fraction	9/16
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	307 mm
Dimension - Length Overall inch	12.09 in
Dimension - N inch	1.12 in
Dimension - Pad Size inch	4 x 4
Dimension - Pad Width inch	4.00 in

Electrical Ratings

Rating - KVA

Conductor Related

Conductor - AL Tube Std Size	5 IPS
Conductor - AL Tube Std Size Range	5 IPS
Conductor - Connection Combination	Tube to Flat
Conductor Type	AL Tube Std-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Product Assets

[3D Models - NBC24ACG3_MODEL-PDF](#)
[3D Models - NBC24ACG3_MODEL-STEP](#)
[3D Models - NBC24ACG3_MODEL-IGES](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - CSC027770-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_CA-NBC24ACG3-SPEC-EN | REV 6/2024