

## BS10, Vinyl Splice, #12-10 AWG

By Burndy  
Catalog # [BS10](#)



Vinyl Splice For 12 - 10 AWG.

### Features

- Manufactured from seamless electrolytic copper tubing to provide maximum conductivity and tensile strength in a high quality design with no seams to split
- Funnel entry for easy wire insertion
- Electro-tin plating provides durable, long lasting resistance to corrosion
- Expanded insulation support to lower inventory requirements
- Vinyl insulation provides an economical means of providing high dielectric values and cable insulation support

### Application

For Accommodating A Broad Range Of 600 Volt Cables

### General

Catalog Number	BS10
Color Code	Yellow
Connector Type	Seamless Butt Splice
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	VINYLINK
Temperature Rating	105
Trade Name	VINYLINK™
Type	BS
UPC	781810805862
UPC 14 Digit GTIN	00781810805862

### Dimensions

Dimension - Diameter Max Size	0.26 in
inch	
Dimension - Length Overall	1.23 in
inch	
Dimension - Outside Diameter	0.26 in
inch	
Dimension - Strip Length	21/64 in

### Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

### Conductor Related

Conductor - Copper Str Size	12 AWG-10 AWG
Range	
Conductor Size	12 - 10 AWG
Conductor Type	CU C Str-Size

### Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards	UL467
Met	
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

### Logistics

Carton Quantity	500
Pallet Quantity	99999

### Product Assets

[3D Models - BS10\\_MODEL-IGES](#)  
[3D Models - BS10\\_MODEL-PDF](#)  
[3D Models - BS10\\_MODEL-STEP](#)  
[Catalogs - BURNDY Master Catalog - Section B - Small Terminals](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_KTFBS\\_LineArt](#)  
[Sales Drawings - 50094190](#)  
[Specifications - BS10 Specification Sheet English](#)  
[Specifications - BS10 Specification Sheet French](#)