



Substation - Copper Coupler - Straight

By Burndy
Catalog # [NS1515HCHQ](#)



Cast Cu Alloy Bolted Coupler, 1" IPS, Silicon Bronze H/W.

Application

Substation

General

Catalog Number	NS1515HCHQ
Connector Type	Couplers
Installation Torque Recommended in-lb	480 LBS/in
Material	Copper Alloy, Cast
Material - Hardware	Silicon Bronze
One Wrench Installation	Y
Physical Attribute - Number of Run Conductors	1
Physical Attribute - Number of Tap Conductors	1
Physical Attribute - Pad Orientation	Straight
Plated	N
Plating Type	Unplated
Type	Tube to Tube Couplers
UPC	781810462577
UPC 12 Digit	7818104625777

Dimensions

Dimension - B Length inch	2.69 in
Dimension - Height inch	2.57 in
Dimension - L Length Overall mm	143 mm
Dimension - Length BB inch	2.69 in
Dimension - Length Overall inch	5.63 in
Dimension - Width inch	3.22 in
Dimension - Width mm	82 mm

Conductor Related

Conductor - Connection Combination	Tube to Tube
Conductor - Copper Tube Std Run	1 IPS
Conductor - Copper Tube Std Size	1 IPS
Conductor - Copper Tube Std Size Range	1 IPS
Conductor - Copper Tube Std Tap	1 IPS
Conductor Type	CU Tube Std-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Product Assets

[3D Models - NS1515HCHQ_MODEL-STEP](#)
[3D Models - NS1515HCHQ_MODEL-PDF](#)
[3D Models - NS1515HCHQ_MODEL-IGES](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section L - Bolted Substation](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 10080987](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_CA-NS1515HCHQ-SPEC-EN | REV 6/2024