




BTCGC250SS, Aluminum Ground Tray Clamp, #6-250 kcmil

By Burndy
Catalog # [BTCGC250SS](#)

Aluminum ground tray clamp, accomodates ground wire size #6 to 250 Kcmil.



Features

- Tin plated aluminum for durable, long lasting corrosion resistance
- cULus 467 Listed for Grounding and Bonding in US and Canada
- cULus 2703 Listed for solar PV applications in US and Canada
- Accommodates most popular styles of cable tray with inside or outside flange
- Quick and easy installation
- no drilling or special tools required
- Set screw bonds clamp to the cable tray while another set screw securely fastens the grounding conductor to the clamp providing vibration resistance and outstanding pull-out values
- Grounding green hardware as required in Section 8.4 of UL2703

General

Allen Key Size	1/4 in
Application	Type BTCGC-SS clamps are suitable for outdoor applications and may be used with most types of cable tray with an inside or outside flange design
Catalog Number	BTCGC250SS
EU RoHS Indicator	Contact Manufacturer
Finish Type	Tin Plated
Material	Aluminum
Material - Hardware	Stainless steel
UPC	621945505957

Dimensions

Dimensions	2.25 in x 0.88 in x 2.43 in
Height	2.43 in
Length	2.25 in
Thickness - Flange Plate	1/2 in
Width	0.88 in

Conductor Related

Conductor - AL Str Size Range	#6 AWG - 250 Kcmil
Conductor - Copper Str Size Range	6 AWG - 250 kcmil
Conductor Range	#6 AWG - 250 Kcmil AL-CU

Certifications And Compliance

Certified Listed	cULus Listed
------------------	--------------

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50087187](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY_CA-BTCGC250SS-SPEC-EN | REV 6/2024