



## CCSC146600, Clear Cold Shrink, 6", .70"-1.05" Jacket OD Range

By Burndy  
Catalog # [CCSC146600](#)

Clear Cold Shrink, Specially formulated silicone rubber offering excellent insulation and moisture resistant sealing for in-line cable connector systems. The rubber sleeves are factory expanded over a removeable, plastic ripcord housing. Installs quickly and easily with no heat gun or other installation tools. Passes TELCORDIA GR-347-CORE Abrasion and Cut Test up to 750 kcmil. Operating temperature range: -40°C to +105°C.



### Features

- Forms a moisture resistant seal
- Indoor and outdoor applications
- Rip and Grip Installation does not require heat gun or any installation tools
- Passes TELCORDIA GR-347-CORE Abrasion and Cut Test up to 750 kcmil
- cUL insulating cover for wire connectors tested in accordance to UL 486A/B
- Passes UL 746C Glow Wire Test
- Ripcord is recyclable

### General

Application	Cold Shrink, Rated to 2000 Volts, offer insulation and moisture resistant sealing for in-line cable connector systems
Catalog Number	CCSC146600
Color	Clear
Connector Type	CLEAR
Material	Silicone Rubber
UPC	621945524224

### Dimensions

Diameter	0.63 in
Dimension - Diameter Max before Shrink inch	1.46
Length	5.91 in
Width	0.1 in

### Electrical Ratings

Voltage Rating	2000 V
----------------	--------

### Certifications And Compliance

Certification - CSA Approved	No
------------------------------	----

### Logistics

Carton Quantity	360
Pallet Quantity	900

### Product Assets

[Catalog Page - BURNDY Page D2 & D3 - Cold Shrink](#)  
[Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 50090656](#)  
[Sell Sheets - Clear & Black Cold Shrink - Rated for 2000 Volts](#)  
[Video - Grease Best PRactices](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRDY\_CA-CCSC146600-SPEC-EN | REV 6/2024