



CCSC200600, Clear Cold Shrink, 6", .90"-1.28" Jacket OD Range

By Burndy
Catalog # [CCSC200600](#)

Clear Cold Shrink, Specially formulated silicone rubber offering excellent insulation and moisture resistant sealing for in-line cable connector systems. The rubber sleeves are factory expanded over a removeable, plastic ripcord housing. Installs quickly and easily with no heat gun or other installation tools. Passes TELCORDIA GR-347-CORE Abrasion and Cut Test up to 750 kcmil. Operating temperature range: -40°C to +105°C.



Features

- Forms a moisture resistant seal
- Indoor and outdoor applications
- Rip and Grip Installation does not require heat gun or any installation tools
- Passes TELCORDIA GR-347-CORE Abrasion and Cut Test up to 750 kcmil
- cUL insulating cover for wire connectors tested in accordance to UL 486A/B
- Passes UL 746C Glow Wire Test
- Ripcord is recyclable

General

Application	Cold Shrink, Rated to 2000 Volts, offer insulation and moisture resistant sealing for in-line cable connector systems
Catalog Number	CCSC200600
Color	Clear
Connector Type	CLEAR
Construction Material - Main	Silicon Rubber
EU RoHS Indicator	Contact Manufacturer
Material	Silicone Rubber
Type	CCSC
UPC	621945524248

Dimensions

Diameter	0.75 in
Dimension - Diameter Max before Shrink inch	2.09
Length	5.91 in
Width	0.12 in

Electrical Ratings

Voltage Rating	2000 V
----------------	--------

Certifications And Compliance

Certification - CSA Approved No

Logistics

Carton Quantity	250
Pallet Quantity	900

Product Assets

[Catalog Page - BURNDY Page D2 & D3 - Cold Shrink Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50090656](#)
[Sell Sheets - Clear & Black Cold Shrink - Rated for 2000 Volts](#)
[Video - Grease Best PRactices](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY_CA-CCSC200600-SPEC-EN | REV 6/2024