



Full Cycle Ratchet Crimper, Dieless,
6000 lbs, Installs Service Entrance
Splice Connectors #10 AWG - #1/0
AWG

By Burndy
Catalog # [OH25](#)

Full Cycle Ratchet Crimper, Dieless, Service Entrance.



General

Application - For Use On	Service Entrance Splices
Catalog Number	OH25
Die Type	Dieless
EU RoHS Indicator	Yes
Tool Type	Full Cycle Ratchet Crimper, Dieless
Trade Name	HYTOOL™
UPC	781810452004
UPC 12 Digit	7818104520044

Dimensions

Dimensions	12.00 in x 0.75 in x 6.25 in
Height	6.25 in
Length	12 in
Weight	2.687 lb
Width	0.75 in

Conductor Related

Crimping Ranges	Aluminum: #10 AWG - #1/0 AWG
-----------------	---------------------------------

Certifications And Compliance

Standards - RoHS Compliance	EX Status
-----------------------------	--------------

Logistics

Package Contents	Tool only
------------------	-----------

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section N - Tooling](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) -
BUR_082_OT8F_OH25_lineart](#)
[Sales Drawings - 210780](#)



A proud member of the Hubbell Family.