



CTNT50400D0, Cable Tie, 50 Lb Tensile, Black, Nylon 12

By Burndy
Catalog # [CTNT50400D0](#)



Nylon 12 Cable Tie.

Features

- Nylon 12 Cable Ties provide excellent UV, chemical and moisture resistant
- Ties feature inside serrations and bent tail for quick, easy installation
- Smooth edge to prevent bundle damage
- Especially suitable in high moisture, corrosive (zinc chloride and dilute acids) environments
- Good in low temperatures
- Indoor/Outdoor applications

General

Catalog Number	CTNT50400D0
Color	Black
Material	NYLON 12
Rating - Minimum Tensile Strength lbs	50 lb
Tensile Strength	50 / 22 lb./Kg
Trade Name	UNIRAP™
UPC	621945469341

Dimensions

Dimension - Bundle Diameter Max inch	4.00 in
Dimension - L Length Overall mm	380 mm
Dimension - Length Overall inch	15.00 in
Dimension - Width inch	0.19 in
Dimension - Width mm	4.8 mm
Thickness	0.06 in

Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	8000
-----------------	------

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50071686](#)
[Specifications - CTNT50400D0 Specification Sheet French](#)
[Specifications - CTNT50400D0 Specification Sheet English](#)



A Hubbell brand