



PENA1/2, Oxide Inhibitor, .5 ounce

By Burndy
Catalog # [PENA1/2](#)

Oxide Inhibiting Electrical Joint Compound, 1/2 OZ, For Al-Al, Al-Cu & Al Conduit Threads.

Features

- PENETROX™ Oxide Inhibiting Joint Compounds are available in many types
- PENETROX A is a natural compound recommended for aluminum to aluminum, aluminum to copper connections and aluminum conduit threads, it is not recommended for use with rubber or polyethylene insulated conductors
- PENETROX A13 is a synthetic base compound with evenly suspended zinc particles recommended for aluminum to aluminum, aluminum to copper, and also aluminum conduit threads
- PENETROX E is a synthetic base with evenly suspended copper particles, recommended for copper to copper, copper threads, and all grounding applications

Application

For Aluminum To Copper, Aluminum To Aluminum, Aluminum To Conduit

General

Application - For Use On	Aluminum to Aluminum;Aluminum to Conduit;Aluminum to Copper
Catalog Number	PENA1/2
Container Type	Tube
EU RoHS Indicator	Yes
Pour Point	-15 °F
Sub Brand	PENETROX
Temperature - Dropping Point Fahrenheit	230 °F
Trade Name	PENETROX™
Type	A

UPC	781810592601
UPC 14 Digit GTIN	00781810592601
Viscosity at 100 Fahrenheit	305 °F

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	50
Container Size	1/2 oz

Product Assets

[Catalogs - BURNDY Master Catalog - Section F - Accessories](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_PENA_LineArt](#)
[Sales Drawings - sc211487-01](#)
[SDS - PENETROX A PORTUGUESE SDS](#)
[SDS - PENETROX A GERMAN SDS \(GHS\) \(2019-07\)](#)
[SDS - PENETROX A ESTONIAN SDS](#)
[SDS - PENETROX A FRENCH SDS](#)
[SDS - PENETROX A ESPANOL SDS](#)
[SDS - PENETROX A SDS](#)
[Specifications - Burndy_PENA12_Specsheet](#)
[Specifications - PENA12 Specification Sheet English](#)
[Specifications - PENA1/2 Specification Sheet French](#)