



PENA138, Oxide Inhibitor, 8 ounce

By Burndy
Catalog # [PENA138](#)

Oxide Inhibiting Electrical Joint Compound, 8 OZ, For Al-Al, Al-Cu & Al Conduit Threads / Insulated Cable



Features

- PENETROX™ Oxide Inhibiting Joint Compounds are available in many types
- PENETROX A is a natural compound recommended for aluminum to aluminum, aluminum to copper connections and aluminum conduit threads, it is not recommended for use with rubber or polyethylene insulated conductors
- PENETROX A13 is a synthetic base compound with evenly suspended zinc particles recommended for aluminum to aluminum, aluminum to copper, and also aluminum conduit threads
- PENETROX E is a synthetic base with evenly suspended copper particles, recommended for copper to copper, copper threads, and all grounding applications

Application

Aluminum to Aluminum, Aluminum to Conduit, Aluminum to Copper

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
EU RoHS Indicator	Yes
UL Listed	Yes
Certification - CSA Approved	No

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

General

Application - For Use On	- Aluminum to Aluminum - Aluminum to Conduit - Aluminum to Copper
Trade Name	PENETROX™
Sub Brand	PENETROX
Container Type	Squeeze Bottle
UPC	781810592571
Type	Sealing compound
Pour Point	-40 °F
UPC 12 Digit	781810592571
UPC 14 Digit GTIN	00781810592571

Logistics

Pallet Quantity	2016
Carton Quantity	12
Container Size	8 oz

Operational

Temperature - Dropping Point	350 °F
Fahrenheit	
Viscosity at 100 Fahrenheit	250 °F

Product Assets

[Catalog \[English\]](#)