



CUW391AE, Deadend Clamp, Aluminum Alloy

By Burndy
Catalog # [CUW391AE](#)

Deadend Clamp, High Strength Al Alloy, 336.4 - 795 kcmil Al,
300 - 636 kcmil ACSR, 11.00" L.



Features

- High strength aluminum clamp for deadending primary distribution lines
- Straight-line design with hot stick lifting-eye, pulling-eye
- Captured, angled U-bolts
- Snub-pocket V-shaped, range-taking conductor groove and galvanized steel U-bolts provide high holding strength

General

Catalog Number	CUW391AE
Connector Type	Deadend
Material	Aluminum Alloy
UPC	781810093252

Dimensions

Dimension - B Length inch	5.19 in
Dimension - Height inch	4.82 in
Dimension - L Length Overall mm	297 mm
Dimension - Length Overall inch	11.68 in
Dimension - Width inch	4.12 in
Dimension - Width mm	105 mm

Conductor Related

Conductor - ACSR Str Size Range	300(26-7 STR) - 636(26-7 STR) kcmil
Conductor - AL Str Size Range	336.4 - 795 kcmil

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_CUW26RE1_LineArt](#)
- [Sales Drawings - 39505](#)

