



EP101HP electric pump with foot control

By Burndy
Catalog # [EP101HPFC](#)

Pump, EP101HP, 10K psi, Foot Control.



Application

Pumping

General

Application - For Use On	Use with 10,000 psi Remote Hydraulic Crimpers and Cutters
Power Source	1 HP 115/230V-AC; 60 Hz Motor
Tool Type	Pump, Electric Hydraulic
Type	Pump
UPC	781810095294
UPC 12 Digit	7818100952944

Dimensions

Dimensions	18.50 in x 11.75 in x 18.75 in
Height	18.75 in
Length	18.5 in
Weight	72 lb
Width	11.75 in

Electrical Ratings

Current Draw Max	10 Amperes
------------------	------------

Certifications And Compliance

Standards - RoHS Compliance Status	EX
------------------------------------	----

Logistics

Package Contents	Pump, Foot Control
------------------	--------------------

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_EP10_LineArt](#)
[Sales Drawings - 20789405](#)



A proud member of the Hubbell Family.