

Substation - Aluminum Rigid Spacer

By Burndy
Catalog # [S2R486ACG1](#)



Rigid 13 IN Spacer, 2303.5 kcmil ASC, 230kV.

Application

Substation

General

Clamping Element Design	2 Piece Design
Connector Type	Spacer
Installation Torque Recommended in-lb	480 in-lb
Material	Aluminum Alloy, Cast
One Wrench Installation	Y
Plated	N
Plating Type	Unplated
UPC	621945257573
UPC 12 Digit	6219452575733

Dimensions

Dimension - B Length inch	2.00 in
Dimension - Height inch	2.75 in
Dimension - L Length Overall mm	216 mm
Dimension - Length Overall inch	8.52 in
Dimension - Width inch	2.00 in
Dimension - Width mm	51 mm

Conductor Related

Conductor - AL Str Size Range	2303.5 kcmil
Conductor - Connection Combination	Cable Spacer
Number of Conductors	2

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Product Assets

[3D Models - S2R486ACG1_MODEL-STEP](#)
[3D Models - S2R486ACG1_MODEL-IGES](#)
[3D Models - S2R486ACG1_MODEL-PDF](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - CSD023113-01](#)