



# Electric Hydraulic Pump, Air Bulb Control with Roll Cage, 10,000 psi

By Burndy  
Catalog # [EPAC10](#)

Electric Hydraulic Pump, Air Bulb Control with Roll Cage, 10,000 psi.



## Application

Pumping

## General

Application - For Use On	Use with 10,000 psi Remote Hydraulic Crimpers and Cutters
Catalog Number	EPAC10
Power Source	1/2 HP @ 3450 RPM, 115V-AC; 60 Hz Motor
Tool Type	Pump, Electric Hydraulic
Type	Pump
UPC	781810033371
UPC 12 Digit	7818100333711

## Dimensions

Dimensions	18.50 in x 11.75 in x 17.5 in
Height	17.5 in
Length	18.5 in
Weight	68 lb
Width	11.75 in

## Electrical Ratings

Current Draw Max 10 Amperes

## Certifications And Compliance

Standards - RoHS Compliance CM Status

## Logistics

Package Contents Pump only

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Catalogs - Section N - Tooling](#)  
[Customer Notices - Prop 65 Notice](#)  
[Product Cross Section Image\(s\) - BUR\\_EPAC10\\_LineArt](#)  
[Sales Drawings - SE..207892-01](#)  
[SDS - ALFLUID SDS](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY\_CA-EPAC10-SPEC-EN | REV 6/2024