



# Nylon Block Fork Terminal For 12 - 10 AWG

By Burndy  
Catalog # [TN108BF](#)

Block Fork (Brazead Seam), 12 AWG - 10 AWG, 6-8, 1.02 in L, Wire strip length: 3/8".



## Application

Power Connector

## General

Catalog Number	TN108BF
Connector Type	Block Fork Terminal
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Nylon
Material	Copper
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYDENT
Trade Name	HYDENT™
Type	Fork Tongue
UPC	781810524145

## Dimensions

Dimension - Bolt Size fraction	#6 - #8
Dimension - L Length Overall mm	26 mm
Dimension - Length Overall inch	1.02 in
Dimension - Pad Width inch	0.33 in
Dimension - Strip Length inch	3/8
Dimension - Stud Size inch	#6;#8
Dimension - Z (inch)	0.29 in

## Conductor Related

Conductor Range	#10 AWG to #12 AWG
Conductor Size	12 - 10 AWG
Conductor Type	<ul style="list-style-type: none"><li>• CU C Solid-Size</li><li>• CU C Str-Size</li></ul>

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	100
-----------------	-----

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Catalogs - Section B - Small Compression](#)  
[Product Cross Section Image\(s\) - BUR\\_TN1010BF\\_LineArt](#)  
[Sales Drawings - 50094182](#)



A proud member of the Hubbell Family.