



# FD64C5T10, Substation - Copper Stud Connector

By Burndy  
Catalog # [FD64C5T10](#)

Copper Stud Connectors.



## Application

Substation

## General

Connector Type	Stud Connector
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Physical Attribute - Number of Holes	4
Physical Attribute - Pad Configuration	3x3 - 4 holes
Physical Attribute - Pad Orientation	In-line
Plated	N
Plating Type	Unplated
Type	Studs
UPC	781810098493
UPC 12 Digit	7818100984933

## Dimensions

Dimension - B Length fraction	1-3/4 in
Dimension - B Length inch	1.75 in
Dimension - Bolt Size fraction	3/8
Dimension - D inch	3.00 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - L Length Overall mm	152 mm
Dimension - Length Overall inch	6.00 in
Dimension - N inch	0.62 in
Dimension - Pad Width inch	3.00 in
Dimension - Pin Diameter fraction	3/4 in
Dimension - Pin Diameter inch	0.750 in
Dimension - Thread Size	3/8-10
Dimension - Threads per inch	10

## Conductor Related

Conductor - Connection Combination Stud to Pad

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - SD079583](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY\_CA-FD64C5T10-SPEC-EN | REV 6/2024

