



FQN14M25X03D, Fully Insulated Nylon Male Quick Disconnect For 16 - 14 AWG (.25 x .03)

By Burndy
Catalog # [FQN14M25X03D](#)



Fully Insulated Brass Male Disconnect, 16-14 AWG, Nylon Insulated, Funnel Entry, Tin Plated.

Features

- Fully insulated connectors eliminate the need for post installation insulation
- Funnel entry barrel opening for quick and easy wire insertion
- Dimpled female socket detent for a firm grip

General

Application	For quickly connecting or disconnecting a terminal
Catalog Number	FQN14M25X03D
Connector Type	Male Quick Disconnect
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Nylon
Material	Brass
Plated	Y
Plating Type	Tin
Sub Brand	FINGRIP
Trade Name	FINGRIP™
Type	Disconnect Connectors
UPC	781810293027
UPC 12 Digit	7818102930277

Dimensions

Dimension - Length Overall inch	0.88 in
Dimension - Strip Length inch	3/8 in
Dimension - Width inch	0.25 in
Dimension - Width mm	6 mm

Electrical Ratings

Voltage - Maximum	300 V
-------------------	-------

Conductor Related

Conductor - Copper Str Size	16 AWG;14 AWG
Conductor - Copper Str Size Range	16 AWG - 14 AWG
Conductor Size	16 - 14 AWG
Conductor Type	CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	300
Pallet Quantity	72000

Product Assets

[3D Models - FQN14M25X03D_MODEL-IGES](#)
[3D Models - FQN14M25X03D_MODEL-PDF](#)
[3D Models - FQN14M25X03D_MODEL-STEP](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_FFQNM_LineArt](#)
[Sales Drawings - 50094211](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY_CA-FQN14M25X03D-SPEC-EN | REV 6/2024