

# UH215, Substation Copper Bus Support, 3.5" IPS, 5" Bolt Dia, 5/8" Bolt

By Burndy  
Catalog # UH215



Cast Cu Alloy Bus Support, 3.5" IPS, 5" Bolt Dia, 5/8" Bolt.

## Application

Substation

## General

Connector Type	Bus Support
Fitting Type	Slip or Rigid
Hardware Type	Cap mounting kit (w/o nuts)
Installation Torque Recommended in-lb	660 in-lb
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Mounting Hardware	5/8-11 x 1" LG
One Wrench Installation	Y
Plated	N
Plating Type	Unplated
Type	Cable or Tube to Insulator Bus Supports
UPC	781810119723
UPC 12 Digit	7818101197233

## Dimensions

Bolt Circle Diameter	5 in
Dimension - B Length inch	3.25 in
Dimension - G inch	4.00 in
Dimension - Height inch	6.50 in
Dimension - Hole Size fraction	11/16
Dimension - Hole Size inch	0.69 in
Dimension - Width inch	6.81 in
Dimension - Width mm	173 mm

## Conductor Related

Conductor - Connection Combination	Base to Tube
Conductor - Copper Tube EH Size	3 1/2 IPS
Conductor - Copper Tube EH Size Range	3 1/2 IPS
Conductor - Copper Tube Std Size	3 1/2 IPS
Conductor - Copper Tube Std Size Range	3 1/2 IPS
Conductor Type	<ul style="list-style-type: none"> <li>• CU Tube Std-Size</li> <li>• CU Tube EH-Size</li> </ul>
Number of Conductors	1

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

## Product Assets

[3D Models - UH215\\_MODEL-IGES](#)  
[3D Models - UH215\\_MODEL-PDF](#)  
[3D Models - UH215\\_MODEL-STEP](#)  
[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - sa007374-01](#)