



K33B344N, Copper, Multiple Outlet Transformer Terminal, 4-Holes, 1/2" Holes, NEMA Spacing, 4/0 Str-500 kcmil Copper

By Burndy
Catalog # [K33B344N](#)



Cast Cu Alloy URD Multiple Transformer Terminal, 4 NEMA Holes, 4/0 Str - 500 kcmil Cu Cable, 9/16" Hole Dia.

General

Catalog Number	K33B344N
Connector Type	Terminal
Material	Copper Alloy
Physical Attribute - Number of Holes	4
Plated	Y
Plating Type	Tin
Trade Name	KA-LUG™
UPC	781810189207
UPC 12 Digit	7818101892077

Dimensions

Dimension - D inch	3 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Hole Size fraction	14/25
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	7.09 in
Dimension - N inch	0.62 in
Dimension - Pad Width inch	3 in

Conductor Related

Conductor - Copper Str Size	4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Size Range	4/0 AWG-500 kcmil

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	EX
Status	
UL Listed	No

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_K33B_URD_TRANSFORMER_FIG3_LineArt](#)
[Sales Drawings - 5430](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY_CA-K33B344N-SPEC-EN | REV 6/2024