



K6B28262N, Cu, Multiple Outlet Transformer Term, Lg Groove: #6-4/0 AWG, Sm Groove: #6 Str-2/0 AWG, 2-Hole, 1/2" Stud, 1.75" Spacing



By Burndy
Catalog # [K6B28262N](#)

Cast Cu Alloy URD Multiple Transformer Terminal, 2-NEMA Holes, #6 - 4/0 AWG (Large Groove) #6 Str - 2/0 AWG (Small Groove), 9/16" Hole Dia.

General

Catalog Number	K6B28262N
Connector Type	Terminal
Material	Copper
Material - Hardware	Brass
Physical Attribute - Number of Holes	2
Plating Type	Unplated
Trade Name	KA-LUG™
UPC	781810189108
UPC 12 Digit	7818101891088

Dimensions

Dimension - D inch	3.19 in
Dimension - Hole Size fraction	14/25
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	7.75 in
Dimension - N inch	0.62 in
Dimension - Pad Width inch	1.15 in

Conductor Related

Conductor - Copper Str Size	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Str Size Range	6 AWG-4/0 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_K6B_URD_TRANSFORMER_FIG1_LineArt](#)
- [Sales Drawings - 50860](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY_CA-K6B28262N-SPEC-EN | REV 6/2024