



KAPO250R, Wire range: 2 -250 kcmil, Torque: 180-300 N lb.

By Burndy
Catalog # [KAPO250R](#)

Wire range: 2 -250 kcmil, Torque: 180-300 N lb.



Features

- AL9CU Dual Rated for both copper and aluminum conductor
- Listed to UL Wire Connector Standard UL486A-486B
- Rated for use with Fine Strand Conductor
- 600 Volt Rated
- Range Taking conductor port
- Plastisol insulated covers provided with each connector

General

Application	Terminate "upsized" conductor and/or fine strand conductor into mechanical connectors found in molded case circuit breakers, panel board equipment, and other switchgear.
Catalog Number	KAPO250R
Connector Type	Offset
Material	Aluminum
Type	2 -250 kcmil Mechanical Pin Adaptor Off-Centered Pin
UPC	621945554153

Dimensions

Dimensions	2.47 in x 1.43 in x 1.81 in
Height	1.81 in
Length	2.47 in
Outside Diameter	1.25
Width	1.43 in

Electrical Ratings

Amperage Rating	290
Voltage Rating	600 V

Conductor Related

Conductor - AL Str Size Range	#2 -250 kcmil
Conductor - Copper DLO Size Range	#2 -250 kcmil
Conductor - Copper Flex H Size Range	#2 -250 kcmil
Conductor - Copper Flex I Size Range	#2 -250 kcmil
Conductor - Copper Flex K Size Range	#2 -250 kcmil
Conductor - Copper Str Run	#2 -250 kcmil
Conductor - Copper Str Size Range	#2 -250 kcmil
Conductor Size	2 AWG-250 KCMIL

Logistics

Carton Quantity	25
Pallet Quantity	2250

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section A - Mechanical Interactive Catalog - BURNDY Full-Line Digital Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY_CA-KAPO250R-SPEC-EN | REV 6/2024