



Uninsulated Ring Terminal For 2 AWG 4 AWG

By Burndy
Catalog # [YAD2CM8E516](#)



Non-Insulated Brazed Barrel Copper Terminal, 5 / 16 ", 1.34 in L, Tin Plated, Ring Tongue.

Application

The YAD uninsulated OEM lug terminal is constructed of electrolytic copper

General

Catalog Number	YAD2CM8E516
Connector Type	Ring Terminal
EU RoHS Indicator	No
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Sub Brand	TERMINALS, HYLUG
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810549148
UPC 12 Digit	7818105491488

Dimensions

Dimension - B Length inch	0.47 in
Dimension - Bolt Size fraction	5/16
Dimension - Hole Size inch	0.33 in
Dimension - L Length Overall mm	34 mm
Dimension - Length Overall inch	1.34 in
Dimension - Outside Diameter inch	0.48 in
Dimension - Pad Width inch	0.63 in
Dimension - Strip Length inch	17/32
Dimension - Stud Size inch	5/16

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Str Size	2 AWG
Conductor Size	4 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Str-Size• CU C Flex-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	1000
-----------------	------

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section B - Small Compression](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_YAD36M20E34_LineArt](#)
[Sales Drawings - SE210981-02](#)



A proud member of the Hubbell Family.