



KAPO350, 350 Kcmil pin adaptor, Torque: 500 N lb, Voltage: 600 V.

By Burndy
Catalog # [KAPO350](#)

350 Kcmil pin adaptor, Torque: 500 N lb, Voltage: 600 V.



Features

- AL9CU Dual Rated for both copper and aluminum conductor
- Listed to UL Wire Connector Standard UL486A-486B
- Rated for use with Fine Strand Conductor
- 600 Volt Rated
- Range Taking conductor port
- Plastisol insulated covers provided with each connector

General

Application	Terminate "upsized" conductor and/or fine strand conductor into mechanical connectors found in molded case circuit breakers, panel board equipment, and other switchgear.
Catalog Number	KAPO350
Connector Type	Offset
Hex Key	3/8 in
Installation Torque	450
Recommended in-lb	
Material	Aluminum
Type	1/0 - 350 Mechanical Pin Adaptor; Off-Centered Pin
UPC	621945493360

Dimensions

Dimension - Strip Length inch	1.11 in
Dimensions	2.75 in x 1.50 in x 2.00 in
Height	2 in
Length	2.75 in
Outside Diameter	1.38 in
Width	1.5 in

Electrical Ratings

Amperage Rating	350 A
-----------------	-------

Conductor Related

Conductor - AL Str Size Range	1/0 AWG - 350 kcmil
Conductor - Copper DLO Size Range	1/0 AWG - 350 kcmil
Conductor - Copper Flex H Size Range	1/0 AWG - 350 kcmil
Conductor - Copper Flex I Size Range	1/0 AWG - 350 kcmil
Conductor - Copper Flex K Size Range	1/0 AWG - 350 kcmil
Conductor - Copper Str Size Range	1/0 AWG - 350 kcmil
Conductor Size	1/0 AWG- 350 KCMIL

Logistics

Carton Quantity	25
Pallet Quantity	2250

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50076514](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY_CA-KAPO350-SPEC-EN | REV 6/2024