



# Uninsulated Ring Terminal For 16 - 14 AWG

By Burndy  
Catalog Number [YAV14H](#)



Copper Compression Lug, Heavy Duty, Ring Tongue with Shroud, 1 Hole w/ Inspection Hole, 20-14 AWG, #8-#10 Stud, Short Barrel, Tin Plated.

## General

Application	For Use On Copper Commercial (Code) Cable, Type AN Aircraft Cable And Extra Flexible Conductors
Connector Type	Ring Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Shrouded
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810024959

## Dimensions

Dimension - B Length fraction	1/4 in
Dimension - B Length inch	0.247 in
Dimension - Bolt Size fraction	#10
Dimension - D inch	0.42 in
Dimension - Length Overall inch	0.95 in
Dimension - N inch	0.16 in
Dimension - Outside Diameter inch	0.24 in
Dimension - Pad Width inch	0.31 in
Dimension - Stud Size inch	#10
Dimension - Z inch	0.24 in

## Conductor Related

Conductor - Copper Str Size	20 AWG;18 AWG;16 AWG;14 AWG
Conductor - Copper Str Size Range	20 AWG-14 AWG
Conductor Size	16 - 14 AWG
Conductor Type	<ul style="list-style-type: none"><li>• CU C Solid-Size</li><li>• CU C Str-Size</li></ul>

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	1000
Pallet Quantity	99999

## Product Assets

[Sales Drawings - 50094162](#)  
[Technical Solutions - BURNDY\\_YAV14H\\_Specsheet](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY\_CA-YAV14H-SPEC-EN | REV 11/2023