



HYTOOL™ Hand-Operated Crimper, BG, C & K grooves

By Burndy
Catalog # [MD638](#)



HYTOOL™ Hand-Operated Crimper, Permanent BG, C & K grooves.

Application

Crimping

General

Application - For Use On	Copper, Aluminum, ACSR, Steel, Copperweld, Alumoweld, 6201, 5005, Compressed and Compact Conductors
Catalog Number	MD638
Crimp Force Capacity	4.5 ton
Die Type	W Die and X Die
Tool Type	Hand Operated Crimper
Trade Name	HYTOOL™
Type	Crimper
UPC	781810011034
UPC 12 Digit	7818100110344

Dimensions

Length	21.62 in
Width	7.25 in

Conductor Related

Crimping Ranges

Taps: Copper: #10 sol. to 2/0 str., Aluminum & ACSR: #14 sol. to 4/0 ACSR; Stirrups: #6 to 4/0 ACSR; Overhead Full Tension Deadends, Full Tension Splices and Terminals: #10 str. to 4/0 ACSR; Installs Splices, Taps or Terminations: #8 to 500 kcmil Copper Stranded, #8 to 350 kcmil Copper Flex, #8 to 350 kcmil Aluminum

Certifications And Compliance

Standards - RoHS Compliance EX
Status

Logistics

Package Contents Tool only

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section N - Tooling](#)
[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - BUR_464750_MD6_MD66_MD637_MD638](#)
[Product Cross Section Image\(s\) - BUR_MD68_LA](#)
[Sales Drawings - sd207013-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_CA-MD638-SPEC-EN | REV 6/2024