



YGF294N50 Grounding Plate, #2 AWG-250 kcmil Cu, 4-Hole, 1/2" Stud, 1-3/4" Spacing

By Burndy
Catalog # [YGF294N50](#)



Compression Grounding Plate; Copper; 4-Hole;
Accommodates: #2 AWG - 250 kcmil; 1/2" Stud; 1-3/4" Stud
Hole Spacing; .94 EFF Thread.

General

Die Index	997
Material	Copper
Physical Attribute - Number of Crimps Required	2
Physical Attribute - Number of Tapped Holes	4
Plated	N
Plating Type	Unplated
Trade Name	HYGROUND®
UPC	781810220542
UPC 12 Digit	7818102205422

Dimensions

Dimension - D inch	3.25 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Height fraction	3-31/50 in
Dimension - Height inch	3.62 in
Dimension - L Length Overall mm	147 mm
Dimension - Length Overall inch	5.78 in
Dimension - Pad Width inch	3.25 in
Dimension - Thread Size	1/2-13
Dimension - Threads per inch	13
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Copper Str Size	2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil
Conductor - Copper Str Size Range	2 AWG-250 kcmil
Conductor Type	CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	NEMA Size Holes
Standards - Industry Standards Met	<ul style="list-style-type: none">UL467IEEE 837
Standards - RoHS Compliance Status	EX
UL Listed	No

Product Assets

[3D Models - YGF294N50_MODEL-PDF](#)
[3D Models - YGF294N50_MODEL-STEP](#)
[3D Models - YGF294N50_MODEL-IGES](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_YGF_Lineart](#)
[Sales Drawings - 50015343](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_CA-YGF294N50-SPEC-EN | REV 6/2024