



# HYTOOL™ Hand-Operated Crimper, Polymer Handles, #14 - 4/0 AWG, Permanent O and D3 grooves

By Burndy  
Catalog # MD78



Crimper, Polymer Handles, #14-4/0 AWG, Permanent O & D3 Grooves.

## Features

- Ergonomically designed, one-piece, composite polymer handles
- Comfort grip handles
- Time-proven steel jaw designs
- No tool adjustment required
- 99,000 crimp/cycle life
- Positive lock, spring loaded die retainer buttons
- PTFE impregnated steel/bronze bushings and stainless steel pins
- Electroless nickel plated jaws and jaw links

## General

Application - For Use On	Copper, Aluminum, ACSR, Steel, Copperweld, Alumoweld, 6201, 5005, Compressed and Compact Conductors
Catalog Number	MD78
Crimp Force Capacity	4.5 ton
Die Type	W and X Die
EU RoHS Indicator	Yes
Tool Type	Hand Operated Crimper
Trade Name	POSI-PRESS™ HYTOOL™
UPC	781810010907
UPC 12 Digit	7818100109077

## Dimensions

Dimensions	25.00 in x 4.50 in x 2.00 in
Height	2 in
Length	25 in
Weight	7 lb
Width	4.5 in

## Conductor Related

### Crimping Ranges

Taps: Copper: #10 sol. to 2/0 str., Aluminum & ACSR: #14 sol. to 4/0 ACSR; Stirrups: #6 to 4/0 ACSR; Overhead Full Tension Deadends, Full Tension Splices and Terminals: #10 str. to 4/0 ACSR; Installs Splices, Taps or Terminations: #8 to 500 kcmil Copper Stranded, #8 to 350 kcmil Copper Flex, #8 to 350 kcmil Aluminum

## Certifications And Compliance

Standards - RoHS Compliance EX  
Status

## Logistics

Package Contents Tool only

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_MD7\\_Lineart](#)
- [Sales Drawings - se207642-01](#)
- [Specifications - MD78 Specification Sheet](#)