




YGIBS346132N Structural Steel Compression Grounding Connector

By Burndy
Catalog # [YGIBS346132N](#)



I-Beam Connector for Copper Cable, 2 Pad Holes, 2 AWG-500 kcmil, 1/2-1/3 IN Stud, i-Beam flange Thickness: .550 IN to .613 IN.

General

Connector Type	Tap
I Beam Style	Standard Beam (Flange Angled)
Material	Copper
Physical Attribute - Number of Tapped Holes	2
Plated	N
Plating Type	Unplated
Trade Name	GROUNDLINK™
Type	Taps
UPC	781810039335
UPC 12 Digit	7818100393355

Dimensions

Dimension - B Length fraction	6 in
Dimension - B Length inch	6.00 in
Dimension - I Beam Thickness Range inch	0.501;0.525;0.550;0.562
Dimension - I Beam Thickness inch	.550" - .613"
Dimension - L Length Overall mm	152 mm
Dimension - Length Overall inch	6.00 in

Conductor Related

Conductor - Copper Str Size	250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Size Range	250 kcmil-500 kcmil
Conductor Type	CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	6
Pallet Quantity	1044

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_YGIBS283382N_LineArt](#)
[Sales Drawings - SD208416-04_B](#)



A proud member of the Hubbell Family.