



# YGLR29C58TN Compression Ground Rod Connector

By Burndy  
Catalog # [YGLR29C58TN](#)



Tin plated Copper Compression Connector, Ground Rod to Grid, 2 AWG (Str.) to 250 kcmil, 5/8" Ground Rod or #5- #6 Rebar.

## General

Connector Type	Tap
Die Index	997
Die Index - Element B	1011
Material	Copper
Physical Attribute - Number of Crimps Required	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	GRIDLOK™
Type	Taps
UPC	781810042878
UPC 12 Digit	7818100428788

## Dimensions

Dimension - B Length fraction	22/25 in
Dimension - B Length inch	0.88 in
Dimension - Ground Rod Size	5/8
Dimension - Height fraction	2-7/50 in
Dimension - Height inch	2.14 in
Dimension - L Length Overall mm	22 mm
Dimension - Length Overall inch	0.88 in

## Conductor Related

Conductor - Copper Str Size A	2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil
Conductor - Copper Str Size A Range	2 AWG-250 kcmil
Conductor - Rebar Tap	5;6
Conductor - Rod Size B	5/8 in
Conductor - Rod Size B Range	5/8 in
Conductor Type	<ul style="list-style-type: none"><li>• CU C Str-Size</li><li>• Rod-Size</li><li>• CU Weld C Str-Size</li></ul>

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	Direct Burial
Standards - Industry Standards Met	UL467;IEEE 837
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	10
Pallet Quantity	2400

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)



A proud member of the Hubbell Family.