



Full Cycle Ratchet Crimper for Nuclear Applications, #22 AWG-10 AWG

By Burndy
Catalog # [MR10G6](#)



Full Cycle Ratchet Crimper for Nuclear Applications, #22-10 AWG.

Application

Crimping

General

Application - For Use On	Nylon Insulated Terminals
Catalog Number	MR10G6
Die Type	Permanent Die Grooves
Tool Type	Hand Operated Crimper
Trade Name	HYTOOL™
Type	Crimper
UPC	781810029961
UPC 12 Digit	7818100299611

Dimensions

Length	11.15 in
--------	----------

Conductor Related

Crimping Ranges	#22 - #10 AWG
-----------------	---------------

Certifications And Compliance

Standards - RoHS Compliance Status	EX
------------------------------------	----

Logistics

Package Contents	Tool only
------------------	-----------

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Product Cross Section Image\(s\) - BUR_MR10G6_LineArt](#)
[Sales Drawings - 30004893](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_CA-MR10G6-SPEC-EN | REV 6/2024