



Heat Shrink Ring Terminal For 12 - 10 AWG

By Burndy
Catalog # [YHSA10K10](#)



Cu Heat Shrink Terminal, Ring Tongue, 10-12 AWG, #10 Stud, 1.15" L, 0.34" W, Serrated bbl, Tin plated, For Use On Cu Cond.

Application

For Use On Copper Conductor

General

Catalog Number	YHSA10K10
Connector Type	Ring Terminal
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Heat shrink
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Sub Brand	HYDENT
Trade Name	HYDENT™
Type	YHS, Heat Shrink
UPC	781810477014
UPC 12 Digit	7818104770144

Dimensions

Dimension - B Length fraction	2/9 in
Dimension - B Length inch	0.22 in
Dimension - Bolt Size fraction	#10
Dimension - Hole Size fraction	1/5
Dimension - Hole Size inch	0.20 in
Dimension - Hole Size mm	4.00 mm
Dimension - L Length Overall mm	29 mm
Dimension - Length Overall inch	1.18 in
Dimension - N inch	0.18 in
Dimension - Pad Width inch	0.34 in
Dimension - Strip Length inch	5/16 in
Dimension - Stud Size inch	#10

Conductor Related

Conductor - Copper Str Size Range	12 AWG - 10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100
Packaging Type	Bag

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section B - Small Compression](#)
[Product Cross Section Image\(s\) - BUR_YHSA18K6_LineArt](#)
[Sales Drawings - 50094158](#)



A proud member of the Hubbell Family.

