



Heat Shrink Ring Terminal For 16 - 14 AWG

By Burndy
Catalog # [YHSA14K10](#)



Cu Heat Shrink Terminal, Ring Tongue, 14-16 AWG, #10 Stud, 1.18" L, 0.32" W, Serrated bbl, Tin plated, For Use On Cu Cond.

Application

For Use On Copper Conductor

General

Catalog Number	YHSA14K10
Connector Type	Ring Terminal
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Heat Shrink
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Sub Brand	HYDENT
Trade Name	HYDENT™
Type	YHS, Heat Shrink
UPC	781810476987
UPC 12 Digit	7818104769877

Dimensions

Dimension - B Length fraction	2/9 in
Dimension - B Length inch	0.22 in
Dimension - Bolt Size fraction	#10
Dimension - Hole Size fraction	1/5
Dimension - Hole Size inch	0.20 in
Dimension - Hole Size mm	5 mm
Dimension - L Length Overall mm	30 mm
Dimension - Length Overall inch	1.18 in
Dimension - N inch	0.17 in
Dimension - Pad Width inch	0.32 in
Dimension - Strip Length inch	5/16
Dimension - Stud Size inch	#10

Conductor Related

Conductor - Copper Solid Size	16 AWG;15 AWG;14 AWG
Conductor - Copper Solid Size Range	16 AWG-14 AWG
Conductor - Copper Str Size	16 AWG;14 AWG
Conductor - Copper Str Size Range	16 AWG - 14 AWG
Conductor Size	16 - 14 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications And Compliance

Standards - RoHS Compliance CM Status

Logistics

Packaging Type Bag

Product Assets

- [Catalogs - Full Line BURNDY Catalog](#)
- [Catalogs - Section B - Small Compression](#)
- [Product Cross Section Image\(s\) - BUR_YHSA18K6_LineArt](#)
- [Sales Drawings - 50094158](#)



A proud member of the Hubbell Family.

