



Heat Shrink Fork Terminal For 16 - 14 AWG

By Burndy
Catalog # [YHSA14K10F](#)



Cu Heat Shrink Spade Terminal, Fork Tongue, 14-16 AWG, #10 Stud, 1.17" L, 0.34" W, Serrated bbl, Tin plated, For Use On Cu Cond.

Application

For Use On Copper Conductor

General

Catalog Number	YHSA14K10F
Connector Type	Fork Terminal
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Heat Shrink
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Tin
Sub Brand	HYDENT
Trade Name	HYDENT™
Type	YHS, Heat Shrink
UPC	781810477069
UPC 12 Digit	7818104770699

Dimensions

Dimension - B Length fraction	2/9 in
Dimension - B Length inch	0.22 in
Dimension - Bolt Size fraction	#10
Dimension - Hole Size fraction	1/5
Dimension - Hole Size inch	0.21 in
Dimension - Hole Size mm	5 mm
Dimension - L Length Overall mm	30 mm
Dimension - Length Overall inch	1.17 in
Dimension - N inch	0.27 in
Dimension - Pad Width inch	0.34 in
Dimension - Strip Length inch	5/16
Dimension - Stud Size inch	#10

Conductor Related

Conductor - Copper Solid Size	16 AWG;15 AWG;14 AWG
Conductor - Copper Solid Size Range	16 AWG-14 AWG
Conductor - Copper Str Size	16 AWG;14 AWG
Conductor - Copper Str Size Range	16 AWG - 14 AWG
Conductor Size	16 - 14 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100
Minimum Pack Quantity	100
Packaging Type	Bag

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section B - Small Compression](#)
[Product Cross Section Image\(s\) - BUR_YHSA18K10F_LineArt](#)
[Sales Drawings - 50094174](#)



A proud member of the Hubbell Family.

