



# Ergonomic Full Cycle Ratchet Crimper, For use on #22-#10 Uninsulated (bare) Terminals and Splices

By Burndy  
Catalog # [MRE1022B](#)



Full Cycle Ratchet Crimper, #22-#10 Bare.

### Application

Crimping

### General

|                          |                                   |
|--------------------------|-----------------------------------|
| Application - For Use On | Uninsulated Terminals and Splices |
| Catalog Number           | MRE1022B                          |
| Die Type                 | Permanent Die Grooves             |
| EU RoHS Indicator        | Yes                               |
| Tool Type                | Full Cycle Ratchet Crimper        |
| Trade Name               | HYTOOL™                           |
| UPC                      | 781810512982                      |
| UPC 12 Digit             | 7818105129822                     |

### Dimensions

|            |                              |
|------------|------------------------------|
| Dimensions | 10.38 in x 3.00 in x 1.00 in |
| Height     | 1 in                         |
| Length     | 10.38 in                     |
| Weight     | 1.3 lb                       |
| Width      | 3 in                         |

### Conductor Related

Crimping Ranges                      Copper: #22 AWG - #10 AWG

### Certifications And Compliance

Standards - RoHS Compliance   EX  
Status

### Logistics

Package Contents                      Tool only

### Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Catalogs - Section N - Tooling](#)  
[Customer Notices - Prop 65 Notice](#)  
[Installation Manuals - BUR\\_30009440\\_SOMI\\_MRE10-22B and MRE10-22NV](#)  
[Product Cross Section Image\(s\) - BUR\\_MRE1022\\_lineart](#)  
[Sales Drawings - 30013557](#)



A proud member of the Hubbell Family.