



YHSA18K10F, Heat Shrink Fork Terminal For 22 - 18 AWG

By Burndy
Catalog # [YHSA18K10F](#)



Heat Shrink Fork Terminal For 22 - 18 AWG.

Features

- Made from pure copper, annealed for maximum strength
- Color-coded, imprinted with wire size
- Serrated barrels offer maximum wire contact and tensile strength
- Electro-tin plated for corrosion resistance

Application

For Use On Copper Conductor

General

Catalog Number	YHSA18K10F
Connector Type	Fork Terminal
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Heat Shrink
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Tin
Sub Brand	HYDENT
Trade Name	HYDENT™
Type	YHS, Heat Shrink
UPC	781810477052
UPC 14 Digit GTIN	00781810477052

Dimensions

Dimension - B Length fraction	2/9 in
Dimension - B Length inch	0.22 in
Dimension - Bolt Size fraction	#10
Dimension - Hole Size fraction	1/5
Dimension - Hole Size inch	0.20 in
Dimension - Hole Size mm	5 mm

Dimension - L Length Overall mm	30 mm
Dimension - Length Overall inch	1.18 in
Dimension - N inch	0.27 in
Dimension - Pad Width inch	0.31 in
Dimension - Strip Length inch	5/16
Dimension - Stud Size inch	#10

Conductor Related

Conductor Size	22 - 18 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100
Minimum Pack Quantity	100
Packaging Type	Bag

Product Assets

[Catalogs - BURNDY Master Catalog - Section B - Small Terminals](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_YHSA18K10F_LineArt](#)
[Sales Drawings - 50094174](#)
[Specifications - YHSA18K10F Specification Sheet English](#)
[Specifications - YHSA18K10F Specification Sheet French](#)



A Hubbell brand