



PENA13GAL, Oxide Inhibitor, Gallon Container

By Burndy

Catalog # [PENA13GAL](#)

Oxide Inhibiting Electrical Joint Compound, 1 Gallon, For Al-Al, Al-Cu & Al Conduit Threads / Insulated Cable.



General

Application	For Aluminum To Copper, Aluminum To Aluminum, Aluminum To Conduit
Application - For Use On	Aluminum to Aluminum;Aluminum to Conduit;Aluminum to Copper
Catalog Number	PENA13GAL
Container Type	Can
EU RoHS Indicator	Yes
Pour Point	-40 °F
Sub Brand	PENETROX
Temperature - Dropping Point Fahrenheit	350 °F
Trade Name	PENETROX™
Type	A13
UPC	781810593028
UPC 12 Digit	7818105930288
Viscosity at 100 Fahrenheit	250 °F

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Container Size	1 Gallon
----------------	----------

Product Assets

- [Catalogs - BURNDY Master Catalog - Section F - Accessories](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_PENA13QT_LineArt](#)
- [Sales Drawings - 50016093](#)
- [SDS - PENETROX A-13 ESPANOL SDS](#)
- [SDS - PENETROX A-13 PORTUGUESE SDS](#)
- [SDS - PENETROX A-13 GERMAN SDS](#)
- [SDS - PENETROX A-13 SDS](#)
- [SDS - PENETROX A-13 ITALIAN SDS](#)
- [SDS - PENETROX A-13 FRENCH SDS](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY_CA-PENA13GAL-SPEC-EN | REV 6/2024