



PENA55GAL, Oxide Inhibitor, 55 gallon drum

By Burndy
Catalog # [PENA55GAL](#)



Sealing Compound, 600 V, Viscosity: 305 At 100 DEG F, Size: 55 GAL, Container: Drum.

Features

- PENETROX™ Oxide Inhibiting Joint Compounds are available in many types
- PENETROX A is a natural compound recommended for aluminum to aluminum, aluminum to copper connections and aluminum conduit threads, it is not recommended for use with rubber or polyethylene insulated conductors
- PENETROX A13 is a synthetic base compound with evenly suspended zinc particles recommended for aluminum to aluminum, aluminum to copper, and also aluminum conduit threads
- PENETROX E is a synthetic base with evenly suspended copper particles, recommended for copper to copper, copper threads, and all grounding applications

General

Application - For Use On	Aluminum to Aluminum;Aluminum to Conduit;Aluminum to Copper
Catalog Number	PENA55GAL
Container Type	Drum
Pour Point	-15 °F
Temperature - Dropping Point Fahrenheit	230 °F
Trade Name	PENETROX™
UPC	781810023587
UPC 14 Digit GTIN	00781810023587
Viscosity at 100 Fahrenheit	305 °F

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Container Size	55 Gallon
----------------	-----------

Product Assets

[Catalogs - BURNDY Master Catalog - Section F - Accessories](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_PENAGAL_LineArt](#)
[Sales Drawings - 50016092](#)
[SDS - PENETROX A PORTUGUESE SDS](#)
[SDS - PENETROX A GERMAN SDS \(GHS\) \(2019-07\)](#)
[SDS - PENETROX A ESTONIAN SDS](#)
[SDS - PENETROX A FRENCH SDS](#)
[SDS - PENETROX A ESPANOL SDS](#)
[SDS - PENETROX A SDS](#)
[Specifications - PENA55GAL Specification Sheet French](#)
[Specifications - PENA55GAL Specification Sheet English](#)



A Hubbell brand