



AYPO400, Compression Pin Adapter, 400 kcmil, .63" Pin Dia, 1.6" Pin Length, AL9CU

By Burndy
Catalog # [AYPO400](#)



Aluminum Compression Pin Adapter, 400 kcmil, 0.63" Plug Dia, 1.60" Plug Length, Al/Cu Rated, Tin Plated.

Application

Wire Termination

General

Catalog Number	AYPO400
Color Code	Pink
Connector Type	OFFSET PIN
Die Index	300
EU RoHS Indicator	Yes
Finish Type	Tin-Plated
Insulation	Y
Insulation Type	Rubber
Material	ALUMINUM
Physical Attribute - Number of Crimps Required	4
Pin Type	Solid
Plated	Y
Plating Type	Tin
Sub Brand	HYPLUG
Temperature Rating	194
Terminal Type	Pin
Trade Name	HYPLUG™
Type	Aluminum Pin Adapters
UPC	781810738467
UPC 12 Digit	7818107384677

Dimensions

Dimension - A Outside Diameter inch	1.31 in
Dimension - B Length fraction	1-1/16 in
Dimension - B Length inch	1.07 in
Dimension - B Outside Diameter inch	0.63 in
Dimension - L Length Overall mm	87 mm
Dimension - Length Overall inch	3.43 in
Dimension - P inch	1.60 in
Dimension - Strip Length inch	1-1/8 in
Equivalent Pin Size	300 kcmil

Electrical Ratings

Voltage - Maximum	35000 V
Voltage Rating	35 kV

Conductor Related

Conductor - AL Str Size	400 KCMIL
Conductor - AL Str Size Range	400 kcmil
Conductor - Copper DLO Size	-
Conductor - Copper Flex I Size	400 KCMIL
Conductor - Copper Str Compact Size	400 KCMIL
Conductor - Copper Str Size	400 KCMIL
Conductor - Copper Str Size Range	400 kcmil
Conductor - Material	ALUMINUM / COPPER
Conductor Size	400 KCMIL
Conductor Type	CODE
Wire Size	400 KCMIL

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	10
Pallet Quantity	2400

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section C - Compression Connections](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50103891](#)



A proud member of the Hubbell Family.