



TN148BF, Nylon Block Fork Terminal For 16 - 14 AWG

By Burndy
Catalog # [TN148BF](#)



Nylon Block Fork Terminal For 16 - 14 AWG.

Features

- Permits rapid, easy installation of the terminal under the screw head without complete removal of the screw
- Designed to fit securely into terminal blocks

Application

Power Connector

General

Catalog Number	TN148BF
Connector Type	Block Fork Terminal
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Nylon
Material	Copper
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYDENT
Trade Name	HYDENT™
Type	Fork Tongue
UPC	781810524206
UPC 14 Digit GTIN	00781810524206

Dimensions

Dimension - Bolt Size fraction	#6 - #8
Dimension - L Length Overall mm	24 mm
Dimension - Length Overall inch	0.95 in

Dimension - Pad Width inch	0.30 in
Dimension - Strip Length inch	3/16
Dimension - Stud Size inch	#6;#8
Dimension - Z (inch)	0.30 in

Conductor Related

Conductor Range	#14 AWG to #16 AWG
Conductor Size	16 - 14 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	100
-----------------	-----

Product Assets

[Catalogs - BURNDY Master Catalog - Section B - Small Terminals](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_TN1010BF_LineArt](#)
[Sales Drawings - 50094182](#)
[Specifications - TN148BF Specification Sheet English](#)
[Specifications - TN148BF Specification Sheet French](#)



A Hubbell brand