



# Y10AC9 Hydraulic OEM Pump Kit with Foot Switch, 7 Qts, 10,000 psi, 5/8 HP 115V-AC 60/50 Hz 11 Amps Full Load

By Burndy  
Catalog # [Y10AC9OEM](#)



Y10AC9 Hydraulic OEM Pump Kit with Foot Switch, Reservoir Volume: 7 Qts, 10,000 psi, 5/8 HP 115V-AC 60/50 Hz 11 Amps Full Load.

## Application

Pumping

## General

Application - For Use On	Use with 10,000 psi Remote Hydraulic Crimpers and Cutters
Catalog Number	Y10AC9OEM
Power Source	5/8 HP 115V-AC Motor; 50/60 Cycle
Tool Type	Pump, Electric Hydraulic
Type	Pump
UPC	781810463017
UPC 12 Digit	7818104630177

## Dimensions

Dimensions	12.37 in x 10.25 in x 15.86 in
Height	15.86 in
Length	12.37 in
Width	10.25 in

## Electrical Ratings

Current Draw Max 11 Amperes

## Certifications And Compliance

Standards - RoHS Compliance EX Status

## Logistics

Package Contents Pump, Foot Control

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Catalogs - Section N - Tooling](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - 10086084](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY\_CA-Y10AC9OEM-SPEC-EN | REV 6/2024