



12-Ton Remote C-Head Crimper, 10,000 psi, Uses U Dies, #8 AWG - 750 kcmil Copper and Aluminum, up to 3/4" Ground Rod

By Burndy
Catalog # [Y35BH](#)



12-Ton Remote C-Head Crimper, Operating Pressure 10,000 psi, Uses U Dies, #8 AWG - 750 kcmil Copper and Aluminum, up to 3/4" Ground Rod.

Application

Crimping

General

Application - For Use On	Copper, Aluminum, ACSR, HYGROUND® Compression Grounding, Ground Rod
Catalog Number	Y35BH
Crimp Force Capacity	12 ton
Die Type	U Die
EU RoHS Indicator	Yes
Tool Type	Remote Hydraulic Crimper
Trade Name	HYPRESS™
UPC	781810408452
UPC 12 Digit	7818104084522

Dimensions

Dimension - Length Overall inch	9.75 in
Dimensions	2.62 in x 4.75 in x 9.25 in
Height	9.25 in
Jaw Width	0.95 in
Length	2.62 in
Weight	8 lb
Width	4.75 in

Conductor Related

Crimping Ranges

Copper #8 str. - 500 kcmil code cable (Grounding Terminals, Grounding Splices); Copper #8 str. - 500 kcmil and up to 3/4" ground rod (Grounding Taps); Copper #8 str. - 750 kcmil code cable, N30 - N500 Navy cable, flexible, and extra flex (Terminals (Bare), Terminals (Insulated), Splices to 400 kcmil only; Aluminum #8 str. - 750 kcmil code cable (Terminals, Splices to 350 kcmil only)

Certifications And Compliance

Standards - RoHS Compliance EX Status

Logistics

Package Contents Tool, Metal Case

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section N - Tooling](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_Y35BH_LinaArt](#)
[Sales Drawings - SE209028-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_CA-Y35BH-SPEC-EN | REV 6/2024