

BIBS3504DB, Direct Burial Submersible Four Conductor Insulated Multi-Tap Connector



By Burndy
Catalog # [BIBS3504DB](#)

Direct Burial UNITAP™, 350 Kcmil -12 AWG Str., 5.03 in L,
Designed specifically for direct burial applications.

Features

- Dual rated for aluminum or copper conductors
- Each unit individually marked for ease of identification
- Supplied with aluminum set-screws
- Supplied with oxide inhibitor pre-installed
- Submersible rated and suitable for Direct Burial

Application

For Outside Direct Burial

General

Catalog Number	BIBS3504DB
Connector Type	Multi Tap
EU RoHS Indicator	Yes
Installation Torque	450 LBS/in
Recommended in-lb	
Insulation	Y
Material	Aluminum
Number Of Ports	4
Plated	N
Plating Type	Unplated
Sub Brand	UNITAP
Temperature Rating	194
Trade Name	UNITAP™
Type	BIBS, Multi-Port - Direct Burial
UPC	781810523605
UPC 12 Digit	7818105236055

Dimensions

Dimension - Height inch	2.46 in
Dimension - Height mm	62 mm
Dimension - L Length Overall mm	128 mm
Dimension - Length Overall inch	5.03 in

Dimension - Strip Length inch	1.125
Dimension - Width inch	4.06 in
Dimension - Width mm	103 mm

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - AL Str Size Range	12 - 350 Str
Conductor - Copper Str Size Range	12 - 350 Str
Conductor Size	12 AWG-350 KCMIL
Conductor Type	<ul style="list-style-type: none">• AL C Str-Size• CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Product Assets

- [Catalogs - UNITAP™ Products](#)
- [Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_BIBS_Lineart](#)
- [Sales Drawings - 30013013](#)
- [Specifications - BIBS3504DB](#)