

CL501TN, Copper Lay-in Lug, Tin Plated

By Burndy
Catalog # [CL501TN](#)

Copper Lay-in Lug, 14-4 AWG, #10 Stud, Tin Plated.



Features

- UL2703 for Solar Applications
- UL467 for Direct Burial

Application

For Direct Burial Applications In Concrete Or Earth, For Fast Lay-In Of The Conductor Without The Need For Cutting Or Breaking, For Solar Panel Grounding

General

| | |
|---------------------|----------------------|
| Catalog Number | CL501TN |
| EU RoHS Indicator | Yes |
| Material | Copper |
| Material - Hardware | Stainless Steel |
| Plated | Y |
| Plating Type | Tin - Electro Plated |
| Sub Brand | QIKLUG |
| Trade Name | QIKLUG |
| Type | Open-Faced |
| UPC | 781810352342 |
| UPC 12 Digit | 7818103523422 |

Dimensions

| | |
|---------------------------------|---------|
| Dimension - D inch | 0.47 in |
| Dimension - Height inch | 0.85 in |
| Dimension - Height mm | 21.6 mm |
| Dimension - Hole Size inch | 0.22 in |
| Dimension - Hole Size mm | 6 mm |
| Dimension - L Length Overall mm | 29 mm |
| Dimension - Length Overall inch | 1.13 in |
| Dimension - N inch | 0.19 in |
| Dimension - Stud Size inch | 17/64 |
| Dimension - Thread Size | - |
| Dimension - Width inch | 0.38 in |
| Dimension - Width mm | 10 mm |

Conductor Related

| | |
|-------------------------------------|--|
| Conductor - Copper Solid Size | 14 AWG;13 AWG;12 AWG;11 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG |
| Conductor - Copper Solid Size Range | 14 AWG-4 AWG |
| Conductor - Copper Str Size | 14 AWG;12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG |
| Conductor - Copper Str Size Range | 14 AWG-4 AWG |
| Conductor Type | CU C Str-Size |

Certifications And Compliance

| | |
|---|-------|
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Certification - UL Listed Direct Burial | Y |
| Certification - UL Recognized | N |
| Certification - cULus | N |
| Industry Standard(s) | UL467 |
| Standards - Industry Standards Met | UL467 |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------|-----|
| Carton Quantity | 700 |
|-----------------|-----|

Product Assets

[3D Models - CL501TN_MODEL-PDF](#)
[3D Models - CL501TN_MODEL-STEP](#)
[3D Models - CL501TN_MODEL-IGES](#)
[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - SC212515-01](#)
[Specifications - CL501TN](#)