



Nylon Ring Terminal For 26 - 20 AWG

By Burndy
Catalog # [YAE22G13](#)

Copper Terminal, Ring Tongue w/o Inspection Hole, Wire Range 26-20 AWG, #4-#6 Stud, Nylon Insulated, Tin Plated, 300 Volts Max.



Application

Types YAE-G and YAE-N terminals are rated 105 Deg C and meet military standard AS25036 Class 2 and SAE-AS7928 requirements

General

Catalog Number	YAE22G13
Color Code	Amber
Connector Type	Ring Terminal
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Nylon
Material	Copper
Military Specification	MS25036
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Sub Brand	INSULUG
Trade Name	INSULUG™
Type	YAE-G
UPC	781810804643
UPC 12 Digit	7818108046433

Dimensions

Dimension - Bolt Size fraction	#4 - #6
Dimension - Hole Size fraction	3/20
Dimension - Hole Size inch	0.15 in
Dimension - Length Overall inch	0.74 in
Dimension - N inch	0.13 in
Dimension - Pad Width inch	0.25 in
Dimension - Strip Length inch	5/32 in
Dimension - Stud Size inch	#4;#5;#6
Dimension - Width inch	0.05 in
Dimension - Z (inch)	0.22 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Str Size	20 AWG
Conductor - Copper Str Size Range	26 AWG - 20 AWG
Conductor Size	26 - 20 AWG
Conductor Type	CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	Military Specified (Mil-Spec)
Standards - Industry Standards Met	Military Specified (Mil-Spec)
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	1000
Pallet Quantity	99999

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section B - Small Compression](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_YAE22G13_LineArt](#)
[Sales Drawings - 50094156](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_CA-YAE22G13-SPEC-EN | REV 6/2024

