



# GD1926, Mechanical Grounding Connector, 2 Cables to Rod or Pipe

By Burndy  
Catalog # [GD1926](#)

Mechanical Grounding Connector, 2 Parallel Cables to Rod or Pipe, 4 AWG ( Sol.) - 2/0 AWG (Str.), 2-1/2" to 2-7/8" Rod, 2-1/2" Pipe.



## Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- One-wrench installation

## Application

For Joining A Range Of Two Parallel Copper Cables To Rod Or Pipe And Burial In Ground Or Concrete

## General

Catalog Number	GD1926
EU RoHS Indicator	Yes
Installation Torque Recommended in-lb	240 LBS/in
Material	Copper Alloy, Cast
Material Type - Screw Plated	DURIUM™ Silicon Bronze N
Plating Type	Unplated
Sub Brand	MECHANICAL CONNECTOR
Type	GD
U Bolt Type	266
UPC	781810260364
UPC 12 Digit	7818102603644

## Dimensions

Dimension - B Length inch	1.38 in
Dimension - Height fraction	5 in
Dimension - Height inch	5.00 in
Dimension - Width fraction	4-1/4 in
Dimension - Width inch	4.19 in
Dimension - Width mm	106 mm

## Conductor Related

Conductor - Copper Solid Size	4;3;2;1;1/0;2/0
Conductor - Copper Solid Size Range	4-2/0
Conductor - Copper Str Size	4;3;2;1;1/0;2/0
Conductor - Copper Str Size B Range	2.5
Conductor - Copper Str Size Range	4-2/0
Conductor - Copper Tube Std Size	2-1/2
Conductor - Copper Tube Std Size Range	2-1/2
Conductor - Rod Size	2 1/2 in
Conductor - Rod Size Range	2 1/2 in

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Catalogs - Section E2 - Mechanical Grounding](#)  
[Customer Notices - Prop 65 Notice](#)  
[Product Cross Section Image\(s\) - BUR\\_gdla](#)  
[Sales Drawings - SD..013775-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY\_MX-GD1926-SPEC-EN | REV 6/2024