

GRC12, Mechanical Ground Rod Clamp, Cable to Rod

By Burndy
Catalog # [GRC12](#)



Mechanical Ground Rod Clamp, For Cable to Rod, High Strength, 10 AWG (Sol)- 2 AWG (Str), 1/2" Drive Rod, 3/8" Stud.

Features

- Rated for Direct Burial in earth or concrete
- UL 467 Listed for the US and Canadian Markets

Application

For Joining A Range Of Cable To Copper Clad, Galvanized Steel, And Stainless Steel Ground Rods, Direct Burial Applications In Earth And Concrete

General

Catalog Number	GRC12
EU RoHS Indicator	Yes
Hardware Type	Silicon Bronze
Material	Copper Alloy
Material - Hardware	Silicon Bronze
Plated	N
Plating Type	Unplated
Sub Brand	MECHANICAL CONNECTOR
Type	GRC, High Strength
UPC	781810230947
UPC 12 Digit	7818102309477

Dimensions

Dimension - B Length inch	0.63 in
Dimension - Height inch	2.06 in
Dimension - Height mm	50.8 mm
Dimension - Length Side B inch	0.63 in
Dimension - Width inch	0.89 in
Dimension - Width mm	23 mm

Conductor Related

Conductor - Copper Solid Size Range	10 AWG
-------------------------------------	--------

Conductor - Copper Str Size Range	10 AWG-2 AWG
Conductor - Rod Size	1/2 in
Conductor Size	#10 AWG Sol - #2 AWG Str
Conductor Type	<ul style="list-style-type: none"> • Rod-Size • CU C Solid-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Product Assets

- [3D Models - GRC12_MODEL-IGES](#)
- [3D Models - GRC12_MODEL-STEP](#)
- [3D Models - GRC12_MODEL-PDF](#)
- [Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_GRC_Lineart](#)
- [Sales Drawings - SA..076868-01](#)
- [Specifications - GRC12](#)