



Radiation Resistant Insulated Ring Terminal For 22 - 18 AWG

By Burndy
Catalog Number [YAES18K50](#)



Radiation Resistant High Temp. Ring Terminal, Pure Elect Cu, Smooth Funnel Entry, W/InspWindow, 18-22 AWG, 600 V, 1/4" Stud, Polyvinylidene Insul, Brazed Seam.

General

Application	For Class 1E Critical Circuits And Non-Critical Nuclear Associated Applications
Color Code	Red
Connector Type	Ring Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Belled
Insulation	Y
Insulation Type	Kynar
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Sub Brand	INSULUG
Trade Name	INSULUG™
Type	Radiation Resistant KYNAR Ring Tongue
UPC	781810027035
UPC 12 Digit	7818100270355

Dimensions

Dimension - Bolt Size fraction	1/4
Dimension - Hole Size fraction	10/37
Dimension - Hole Size inch	0.27 in
Dimension - L Length Overall mm	28 mm
Dimension - Length Overall inch	1.09 in
Dimension - Pad Width inch	0.46 in
Dimension - Strip Length inch	7/32 in
Dimension - Stud Size inch	1/4
Dimension - Z inch	0.41 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Solid Size	22 ;20 ;18 AWG
Conductor - Copper Solid Size Range	22 -18 AWG
Conductor - Copper Str Size	22 AWG;20 AWG;18 AWG
Conductor - Copper Str Size Range	22 AWG - 18 AWG
Conductor Size	22 - 18 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Str-Size• CU C Solid-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	1000
Pallet Quantity	99999

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50094159](#)
[Technical Solutions - BURNDY_YAES18K50_Specsheet](#)



A proud member of the Hubbell Family.

