

K11A39U2, Aluminum Universal Terminal, 2 Hole, Two: 1/0 AWG (Str)-750 kcmil, 3/8" Stud, 1.38" Stud Hole Spacing, 2 Screws, Al/Cu Rated, Tin Plated.



By Burndy
Catalog # [K11A39U2](#)

Aluminum Universal Terminal, 2 Hole, Two: 1/0 AWG (Str)-750 kcmil, 3/8" Stud, 1.38" Stud Hole Spacing, 2 Screws, Al/Cu Rated, Tin Plated.

Features

- Constructed from high strength, extruded aluminum alloy
- Electro tin-plated to provide low contact resistance

Application

For Aluminum and Copper Conductors

General

Catalog Number	K11A39U2
Connector Type	Stacked
EU RoHS Indicator	No
Hex Key	3/8
Installation Torque	375 LBS/in
Recommended in-lb	
Material	Aluminum
Material - Hardware	Aluminum
Physical Attribute - Number of Holes	2
Physical Attribute - Screw Type	Allen
Plated	Y
Plating Type	Tin plated
Sub Brand	UNIVERSAL TERM
Temperature Rating	194
Type	Bolted Lugs & Terminals
UPC	781810370292
UPC 12 Digit	7818103702922

Dimensions

Dimension - Bolt Hole Size inch	0.38 in
Dimension - Bolt Size fraction	3/8
Dimension - D inch	2.31 in
Dimension - Height fraction	3 in
Dimension - Height inch	3.02 in
Dimension - Height mm	76.7 mm
Dimension - Hole Size inch	0.41 in
Dimension - Hole Size mm	10 mm

Dimension - L Length Overall mm	125 mm
Dimension - Length Overall inch	4.91 in
Dimension - N inch	0.38 in
Dimension - Pad Width inch	1.52 in
Dimension - Screw Size inch	13/16
Dimension - Stud Size fraction	3/8
Dimension - Stud Size inch	3/8 in
Dimension - Width fraction	1-69/100 in
Dimension - Width inch	1.52 in
Dimension - Width mm	43 mm

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - AL Str Size	1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil;397 kcmil;400 kcmil;450 kcmil;477 kcmil;500 kcmil;550 kcmil;556 kcmil;600 kcmil;636 kcmil;650 kcmil;700 kcmil;715 kcmil;750 kcmil
Conductor - AL Str Size Range	1/0 AWG (Str)-750 kcmil
Conductor - Copper Solid Size	1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Solid Size Range	1/0 AWG-4/0 AWG
Conductor - Copper Str Size	1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil
Conductor - Copper Str Size Range	1/0 AWG (Str)-750 kcmil
Conductor Size	1/0 AWG-750 KCMIL

Conductor Type	<ul style="list-style-type: none"> • AL C Str-Size • CU C Str-Size • CU C Solid-Size 	UL Listed	Yes
----------------	-----------------------------------------------------------------------------------------------------------------------	-----------	-----

Number of Conductors 2

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - UL Listed Direct	No
Burial	
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	NC

Product Assets

- [3D Models - K11A39U2_MODEL-STEP](#)
- [3D Models - K11A39U2_MODEL-PDF](#)
- [3D Models - K11A39U2_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_K22AU_Lineart](#)
- [Sales Drawings - se210997](#)
- [Specifications - K11A39U2](#)

